FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M10X75

Article number	01000.100.075
Brand	-
UBB	950351006016
UNSPSC	31161620
EAN	8715492007681
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
ASME	B18.2.3.1M
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	75
P	1.5
s	17

Technical Drawing

