FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M10X200

Article number	01000.100.200
Brand	-
UBB	950351007261
UNSPSC	31161620
EAN	8715492007865
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	200 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	200
P	1.5
s	17

Technical Drawing

