FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M12X55

Article number	01000.120.055
Brand	-
UBB	950351007592
UNSPSC	31161620
EAN	8715492007957
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	55 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	55
P	1.75
s	19

Technical Drawing

