

## Hexagon head bolt DIN 931 Steel Plain 8.8 M12X110

Article number	01000.120.110
Brand	-
UBB	950351008335
UNSPSC	31161620
EAN	8715492008060
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M12
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

### Standards

NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M
NEN	1555

### Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	110
P	1.75
s	19

### Technical Drawing

