FABORY

# Hexagon head bolt DIN 931 Steel Plain 8.8 M14X70

| | |
|---|---|
| Article number | 01000.140.070 |
| Brand | - |
| UBB | 950351903881 |
| UNSPSC | 31161620 |
| EAN | 8715492008282 |
| PKG. of 50 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M14 |
| Length | 70 mm |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| NF | E25-112 |
| ASME | B18.2.3.1M |
| NEN | 1555 |
| ISO | 4014 |
| DIN | 931 |

## Technical Specification

| | |
|---|---|
| b (min.): 125mmL≤200mm | 40 |
| b (min.): L200mm | 53 |
| b (min.): L≤125mm | 34 |
| d-D | M14 |
| k | 8.8 |
| L (mm) | 70 |
| P | 2 |
| s | 22 |

## Technical Drawing

