FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M16X150

Article number	01000.160.150
Brand	-
UBB	950351012527
UNSPSC	31161620
EAN	8715492008633
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	150
P	2
s	24

Technical Drawing

