FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M16X190

Article number	01000.160.190
Brand	-
UBB	950351914029
UNSPSC	31161620
EAN	8715492008671
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	190 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	190
P	2
s	24

Technical Drawing

