FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M16X230

Article number	01000.160.230
Brand	-
UBB	950351914284
UNSPSC	31161620
EAN	8715492008718
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	230 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	230
P	2
s	24

Technical Drawing

