FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M18X120

Article number	01000.180.120
Brand	-
UBB	950351014275
UNSPSC	31161620
EAN	8715492008947
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	48
b (min.): L200mm	61
b (min.): L≤125mm	42
d-D	M18
k	11.5
L (mm)	120
P	2.5
s	27

Technical Drawing

