FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X170

Article number	01000.200.170
Brand	-
UBB	950351914441
UNSPSC	31161620
EAN	8715492009302
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	170 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
ISO	4014
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	170
P	2.5
s	30

Technical Drawing

