FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M30X340

Article number	01000.300.340
Brand	-
UBB	950351026154
UNSPSC	31161620
EAN	8715492010681
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M30
Length	340 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NEN	1555
NF	E25-112
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	340
P	3.5
s	46

Technical Drawing

