FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M33X170

Article number	01000.330.170
Brand	-
UBB	950351027483
UNSPSC	31161620
EAN	8715492010841
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M33
Length	170 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	170
P	3.5
s	50

Technical Drawing

