FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M36X260

Article number	01000.360.260
Brand	-
UBB	950351029877
UNSPSC	31161620
EAN	8715492011206
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M36
Length	260 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	84
b (min.): L200mm	97
b (min.): L≤125mm	78
d-D	M36
k	22.5
L (mm)	260
P	4
s	55

Technical Drawing

