FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M42X120

Article number	01000.420.120
Brand	-
UBB	950351032582
UNSPSC	31161620
EAN	8715492011596
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M42
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
NEN	1555
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	96
b (min.): L200mm	109
b (min.): L≤125mm	90
d-D	M42
k	26
L (mm)	120
P	4.5
s	65

Technical Drawing

