FABORY

Hexagon head bolt DIN 931 Steel Plain 8.8 M42X500

Article number	01000.420.500
Brand	-
UBB	950351033812
UNSPSC	31161620
EAN	8715492011831
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M42
Length	500 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
DIN	931
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	96
b (min.): L200mm	109
b (min.): L≤125mm	90
d-D	M42
k	26
L (mm)	500
P	4.5
s	65

Technical Drawing

