
FABORY



Hexagon fit bolt with long thread DIN 609 Steel Plain 8.8 M8X70X54,6

Article number	01040.080.070
Brand	-
UBB	500644607490
UNSPSC	31161620
EAN	8717077009295
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M8
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	609

Technical Specification

b:50mmL≤150mm	16.5
b (min.): L150mm	21.5
b:L≤50mm	14.5
d-D	M8
ds (k6)	9
k	5.3
L (mm)	70
Lg (max.)	54.6
P	1.25
s	13
Tolerance drill ø	H7

Technical Drawing

