
FABORY



Hexagon fit bolt with long thread DIN 609 Steel Plain 10.9 M10X35X18,9

Article number	01041.100.035
Brand	-
UBB	500647898658
UNSPSC	31161620
EAN	8717077279957
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	35 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.


Standards

DIN	609

Technical Specification

b:50mmL≤150mm	19.5
b (min.): L150mm	24.5
b:L≤50mm	17.5
d-D	M10
ds (k6)	11
k	6.4
L (mm)	35
Lg (max.)	18.9
P	1.5

Technical Drawing



s	16
Tolerance drill ø	H7