FABORY



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 90 M5X8

Article number	01049.050.008
Brand	-
UBB	500577288219
UNSPSC	31161620
EAN	8715494322515
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	≈6921

Technical Specification

d-D	M5
dc	11.2
k	4.3
L (mm)	8
P	0.8
s	8

Technical Drawing

