FABORY



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 100 M16X30

Article number	01049.160.030
Brand	-
UBB	500644988635
UNSPSC	31161620
EAN	8717077048515
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	30 mm
Class	100
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	≈6921

Technical Specification

d-D	M16
dc	31
k	11.2
L (mm)	30
P	2
s	22

Technical Drawing

