FABORY



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Plain 90 M6X12

Article number	01050.060.012
Brand	-
UBB	950351122912
UNSPSC	31161620
EAN	8715492018977
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	12 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	≈6921

Technical Specification

d-D	M6
dc	14.2
k	5.5
L (mm)	12
P	1
s	10

Technical Drawing

