FABORY



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 90 M5X8

Article number	01055.050.008
Brand	-
UBB	500644989476
UNSPSC	31161620
EAN	8717077048591
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921

Technical Specification

d-D	M5
dc	11.2
k	4.3
L (mm)	8
P	0.8
s	8

Technical Drawing

