FABORY



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 90 M8X25

Article number	01055.080.025
Brand	-
UBB	500571175388
UNSPSC	31161620
EAN	8715494147392
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	25 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921

Technical Specification

d-D	M8
dc	18.2
k	7
L (mm)	25
P	1.25
s	13

Technical Drawing

