FABORY



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M24X440

Article number	01200.240.440
Brand	-
UBB	500644632894
UNSPSC	31161620
EAN	8717077012172
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	440 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	440
P	3
s	36

Technical Drawing

