FABORY



Hexagon head screw ISO 4017/ DIN 933 Steel Zinc plated 8.8 M3X10

Article number	01210.030.010
Brand	-
UBB	950351060617
UNSPSC	31161620
EAN	8715492029225
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4017
ASME	B18.2.3.1M
NF	E25-114
NEN	1568
DIN	933

Technical Specification

d-D	M3
k	2
L (mm)	10
P	0.5
s	5.5

Technical Drawing

