FABORY



Hexagon head screw DIN 933 Steel Zinc plated 8.8 M10X75/S=17

Article number	01210.100.075
Brand	-
UBB	950351070699
UNSPSC	31161620
EAN	8715492030474
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4017
NEN	1568
NF	E25-114
DIN	933
ASME	B18.2.3.1M

Technical Specification

d-D	M10
k	6.4
L (mm)	75
P	1.5
s	17

Technical Drawing

