FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M4X40

Article number	01220.040.040
Brand	-
UBB	954351334006
UNSPSC	31161620
EAN	8715492032935
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
ISO	4014
NEN	1555

Technical Specification

b (min.): L≤125mm	14
d-D	M4
k	2.8
L (mm)	40
P	0.7
s	7

Technical Drawing

