FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M5X50

Article number	01224.050.050
Brand	-
UBB	500648268570
UNSPSC	31161620
EAN	8717077232518
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
NEN	1555
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	50
P	0.8
s	8

Technical Drawing

