FABORY

# Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M6X30

| | |
|---|---|
| Article number | 01224.060.030 |
| Brand | - |
| UBB | 500648268653 |
| UNSPSC | 31161620 |
| EAN | 8717077232525 |
| PKG. of 500 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M6 |
| Length | 30 mm |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated with thick Cr(III+) passivation |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| ASME | B18.2.3.1M |
| ISO | 4014 |
| DIN | 931 |
| NEN | 1555 |
| NF | E25-112 |

## Technical Specification

| | |
|---|---|
| b (min.): 125mmL≤200mm | 24 |
| b (min.): L≤125mm | 18 |
| d-D | M6 |
| k | 4 |
| L (mm) | 30 |
| P | 1 |
| s | 10 |

## Technical Drawing

