FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M24X140

Article number	01224.240.140
Brand	-
UBB	500648278975
UNSPSC	31161620
EAN	8717077233553
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

NEN	1555
ISO	4014
ASME	B18.2.3.1M
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	140
P	3
s	36

Technical Drawing

