FABORY

Hexagon head screw ISO 4017 Steel Zinc plated with thick Cr(III) passivation 8.8 M3X12

Article number	01237.030.012
Brand	-
UBB	500648279544
UNSPSC	31161620
EAN	8717077233614
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	12 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

ISO	4017
NF	E25-114
NEN	1568
ASME	B18.2.3.1M
DIN	933

Technical Specification

d-D	M3
k	2
L (mm)	12
P	0.5
s	5.5

Technical Drawing

