FABORY

Hexagon head screw ISO 4017 Steel Zinc plated with thick Cr(III) passivation 8.8 M3X25

Article number	01237.030.025
Brand	-
UBB	500648279882
UNSPSC	31161620
EAN	8717077233645
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	25 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	933
NEN	1568
NF	E25-114
ISO	4017

Technical Specification

d-D	M3
k	2
L (mm)	25
P	0.5
s	5.5

Technical Drawing

