
FABORY



Hexagon flange bolt with serrated flange, DIN ≈6921 Steel Zinc plated 8.8 M8X16

Article number	01258.080.016
Brand	-
UBB	954351276421
UNSPSC	31161620
EAN	8715492041326
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	16 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Specific features of hexagon bolts with serrated flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.The serrated flange rim gives excellent self-locking properties.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

ISO	≈4162
EN	≈1665
ASME	≈B18.2.3.4M
DIN	≈6921

Technical Specification

d-D	M8
dc (max.)	18
k (max.)	8.1
L (mm)	16
P	1.25
s	13

Technical Drawing

