FABORY

Hexagon nut DIN 934 Steel Zinc plated |8| M3

Article number	01300.030.001
Brand	-
UBB	950355011962
UNSPSC	31161727
EAN	8715492042033
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M3
Class	|8|
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1560
NF	E25-401
DIN	934

Technical Specification

d-D	M3
m	2.4
P	0.5
s	5.5

Technical Drawing

