FABORY

Hexagon nut DIN 934 Steel Zinc plated yellow passivated |8| M20

Article number	01320.200.001
Brand	-
UBB	950355018652
UNSPSC	31161727
EAN	8715492042934
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M20
Class	|8|
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-401
NEN	1560
DIN	934

Technical Specification

d-D	M20
m	16
P	2.5
s	30

Technical Drawing

