FABORY

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M8X50

Article number	01400.080.050
Brand	-
UBB	950351187287
UNSPSC	31161620
EAN	8715492408099
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating.After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.ISO metric

Standards

ASME	B18.2.3.1M
ISO	4014
NEN	1555
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22

Technical Drawing

d-D	M8
k	5.3
L (mm)	50
P	1.25
s	13

