FABORY

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M27X160

Article number	01400.270.160
Brand	-
UBB	950351198094
UNSPSC	31161620
EAN	8715492409652
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	160 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating.After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.ISO metric

Standards

NEN	1555
DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79

Technical Drawing

b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	160
P	3
s	41

