FABORY

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M33X120

Article number	01400.330.120
Brand	-
UBB	950351941584
UNSPSC	31161620
EAN	8715492409812
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating.After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.ISO metric

Standards

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91

Technical Drawing

b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	120
P	3.5
s	50

