FABORY

Hexagon nut ISO-Metric thread ISO 4032 Steel Hot dip galvanized 8 M24

Article number	01510.240.001
Brand	-
UBB	500613234524
UNSPSC	31161727
EAN	8715494433303
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously as the thread will be protected by the zinc

Standards

ISO	4032

layer of the mating part.ISO metric

Technical Specification

d-D	M24
m (max.)	21.5
P	3
s	36

Technical Drawing

