FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated 10.9 M10X180

Article number	04101.100.180
Brand	-
UBB	500648298510
UNSPSC	31161620
EAN	8717077206809
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	180 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	180
P	1.5
s	16

Technical Drawing

