FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated 10.9 M12X70

Article number	04101.120.070
Brand	-
UBB	500648299195
UNSPSC	31161620
EAN	8717077206861
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	70 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-112
ISO	4014
DIN	931
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	70
P	1.75
s	18

Technical Drawing

