FABORY

Hexagon head bolt DIN 931 Steel Zinc plated 10.9 M8X55

Article number	04102.080.055
Brand	-
UBB	500648125929
UNSPSC	31161620
EAN	8717077208469
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	55 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NEN	1555
NF	E25-112
ISO	4014
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	55
P	1.25
s	13

Technical Drawing

