FABORY

Hexagon head bolt DIN 931 Steel Zinc plated 10.9 M24X300

Article number	04102.240.300
Brand	-
UBB	500648140936
UNSPSC	31161620
EAN	8717077209961
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	300 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NEN	1555
NF	E25-112
ASME	B18.2.3.1M
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	300
P	3
s	36

Technical Drawing

