FABORY

Hexagon head bolt DIN 931 Steel Dacromet 500 LC Grade A 10.9 M14X60/S=22

Article number	04103.140.060
Brand	-
UBB	954351244585
UNSPSC	31161620
EAN	8715492116826
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	60 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Dacromet 500 LC Grade A
Thread	Metric thread

Standards

DIN	931
NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	60
P	2
s	22

Technical Drawing

