FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M16X70

Article number	04104.160.070
Brand	-
UBB	953351910377
UNSPSC	31161620
EAN	8715493175747
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	70 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
ISO	4014
DIN	931
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	70
P	2

Technical Drawing

