FABORY

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M24X100

Article number	04104.240.100
Brand	-
UBB	500614317765
UNSPSC	31161620
EAN	8715494454643
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	100 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
ASME	B18.2.3.1M
NEN	1555
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	100
P	3

Technical Drawing

