FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M10X45

Article number	04105.100.045
Brand	-
UBB	500505560705
UNSPSC	31161620
EAN	8715494439084
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	45 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NF	E25-112
DIN	931
NEN	1555
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	45
P	1.5

Technical Drawing

