FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M10X50

Article number	04105.100.050
Brand	-
UBB	500505560887
UNSPSC	31161620
EAN	8715494439107
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	50
P	1.5

Technical Drawing

