FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M12X100

Article number	04105.120.100
Brand	-
UBB	500505562115
UNSPSC	31161620
EAN	8715494439343
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	100 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
DIN	931
NEN	1555
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	100
P	1.75

Technical Drawing

