FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M16X65

Article number	04105.160.065
Brand	-
UBB	500575130413
UNSPSC	31161620
EAN	8715494313995
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	65 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	65
P	2

Technical Drawing

