FABORY

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M16X100

Article number	04105.160.100
Brand	-
UBB	500505563360
UNSPSC	31161620
EAN	8715494439558
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	100 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
NEN	1555
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	100
P	2

Technical Drawing

